

SOCKET 1/2 INCH DRIVE 12 POINT 19MM

Item ID: M120519-C



- 1/2" drive regular metric 12 point socket
- Chrome vanadium
- Satin finish for a better grip when handling the socket
- 12 point bi-hexagon socket for easier alignment to the fastening
- Teng Tools hip grip design for contact with the flat side of the fastening for reduced damage and use on rounded nuts and bolts
- Ball bearing recess on the female end to grip the ratchet or power bar
- Designed and manufactured to DIN3120/3124 and ISO2725
- Supplied with a metal socket clip for use with a socket rail

Length (mm): 26

Width (mm): 45

Height (mm): 90

Weight (g): 70



Technical changes and errors may occur

WWW.TENGOOLS.COM



Get organised™