



Save as PDF



Peli protector cases - Watertight protector cases - 1610 case



Interior dimensions:
55 x 42.2 x 26.8 cm (22" x 17" x 11")

Watertight, crushproof, and dust proof

- Easy-open, double-step latches
- Open cell core with solid wall design - strong, light weight
- O-ring seal
- Automatic Pressure Equalization Valve
- Fold down handles
- Stainless steel hardware and padlock protectors
- 3 layer Pick 'N' Pluck™ foam with convoluted lid foam
- Personalised nameplate service available
- Unconditionally Guaranteed

Retractable extension handle

Strong polyurethane wheels with stainless steel bearings



Black

Peli protector cases - Watertight protector cases - 1610 case SPECIFICATIONS

Exterior Dimensions (L x W x D)		Interior Dimensions (L x W x D)	
62.7 x 49.7 x 30.3 cm (25" x 20" x 12")		55 x 42.2 x 26.8 cm (22" x 17" x 11")	
Lid Depth	Bottom Depth	Total Depth	
5.2 cm (2")	21.6 cm (8.50")	26.8 cm (10.56")	
Lid Depth	Bottom Depth	Total Depth	
5.2 cm (2.06")	21.6 cm (8.50")	26.8 cm (10.56")	
Weight w/Foam	Weight w/o Foam	Buoyancy Max.	
10.2 kg. (22.49 lbs)	9.07kg (20 lbs.)	54.4 kg (119.93 lbs.)	
Range Temperature	No. of Wheels	Retractable Handle	
-40 / 99° C (-40 / 210° F)	2	Yes	

Personalized Nameplate Available

1610EU Case Certificates

- IP67(1 meter submersion for 30 minutes)
- Def Stan 81-41/STANAG 4280

Materials

Body	Latch	Lid O-Ring	Pins
Polypropylene	ABS	Polymer	Stainless Steel
Foam	Purge Body	Purge Vent	Purge O-Ring
1.3 lb Polyurethane	ABS	3 Micron Hydrophobic Non- Woven PET	70 Shore Nitrile

Configuration

Cat. #	Description
1610EU	Peli protector cases - Watertight protector cases - 1610 case

Peli protector cases - Watertight protector cases - 1610 case Accessories

Cat. #	Description