

Product datasheet

Specifications



APC NetShelter Rack PDU Advanced Gen 2, Metered, 7.4kW, 1Phase, 230V, 32A, 332P6, 40 Outlets

APDU11150ME

Main

Colour	Black
Product or component type	PDU
PDU type	Metered
Cord length	3 m

Complementary

Input Voltage	230 V 1 phase
Height	1490 mm
Width	56 mm
Output Voltage	230 V
Depth	75 mm
Product weight	6.2 kg
Mounting location	Side
Mounting preference	No preference
Input Plug Type	IEC 60309 32 A 2P + PE
mounting mode	Rack-mounted
Rack units	0U
Mounting position	Vertical
Communication port protocol	1000BASE-T 10/100BASE-T
[In] rated current	32 A
permissible voltage	200...240 V
Input current limits	32 A
Load capacity	7400 VA
Network frequency	50/60 Hz
Outlet type and quantity	20 C13/C15/C19/C21 20C13/C15

Environment

Product certifications	UKCA
Standards	CE EN 62368-1

Packing Units

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	172 cm
Package 1 Width	11.6 cm
Package 1 Length	20.8 cm
Package 1 Weight	8.2 kg

Logistical informations

Country of origin	US
-------------------	----

Contractual warranty

Warranty (in months)	36
----------------------	----



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Use Better

Materials and Substances	
Packaging made with recycled cardboard	No
Packaging without single use plastic	No
SCIP Number	31346aed-552c-4a16-81d9-e683a383b6da
EU RoHS Directive	Compliant By Exemption
REACH Regulation	Reference contains Substances of Very High Concern above the threshold

Use Longer

Lifetime extension	
Repair	No

Use Again

Repack and remanufacture	
Removable battery	No
Take-back	No
WEEE Label	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Image of product / Alternate images

Alternative

