

**3310016001**

## STATYS XS 1STAXS 16A 2W2P 230V



Provides redundant power supply to single-corded It equipment.

### Strong points

- Ensured power continuity
- Easy rack integration
- Hot-swappable version
- Agility and ease of use
- Flexible remote management

### General characteristics

- Competitive alternative to redundant power supply at IT equipment level (dual corded).
- Easy to install and use (Plug and play).
- Ease of use - Intuitive operation.
- Numerous outlets to connect IT equipment.
- Ethernet connection capability for remote monitoring.
- Fast and secured module replacement with no load interruption.

### Compliance with standards

- IEC 60950-1
- CEI/EN 62310-2
- WEEE
- ROHS
- CE

### Access to resources (ex: manuals)

### Technical Characteristics

Length of the product unit [mm]	44
Width of the product unit [mm]	440
Depth of the product unit [mm]	285
Weight [kg]	4
Depth [mm]	285
Height [mm]	44
In/out	1/1
Number of poles	2
Output voltage	230
Rated frequency	50/50
Rated current [A]	16
Width [mm]	440
Input voltage	230
Rate (min)	16
Rate (max)	16
Switching Poles	2P

### Classification

ETIM Class	EC002850
------------	----------

### Commerce

Description	STATYS XS 16A 230V SINGLE PHASE 2 WIRES 2 POLE SWITCHING 19 INCHES RACK
Effective date	2018-06-01
Offer Life Cycle Code	40
Country of origin	CN

### Logistics

GTIN/EAN	3596033031434
Customs number	8536500500
Weight of the packing unit [kg]	4
Length of the packing unit [m]	0.285
Width of the packing unit [m]	0.44
Depth of the packing unit [m]	0.044

### Norms

Conformity to standards	IEC
-------------------------	-----