



ENGLISH

## Datasheet

Stock No: 258-2318

# RS Pro 7094842 Analogue Positive Pressure Gauge Bottom Entry 1bar, Connection Size G 1/2



## Product Details

**100mm Diameter Pressure and Vacuum Gauges - Stainless Steel Construction**

Suitable for corrosive environments and gaseous or liquid media that will not destruct the pressure system

Laminated Safety Glass Window

316TI Stainless Steel Element & Movement

304 stainless Steel case with G 1/2 in. BSPM connection

Bottom entry connection

Ambient Operating Temperature between -20 and +60°C

Operating Temperature (Medium) +100°C

1.6 Per DIN 16005 Accuracy Class



ENGLISH

## Specifications:

Minimum Pressure Measurement	-1bar
Maximum Pressure Measurement	1bar
Pressure Gauge Type	Bottom Entry
Gauge Outside Diameter	100mm
Connection Size	G 1/2
Case Material	Stainless Steel
Minimum Operating Temperature	-20°C
Maximum Operating Temperature	+60°C