

Reciprocating Saw

JR3051TK

JR3051T is a mains powered reciprocating saw with a higher continuous input rating than its predecessor and a shorter overall length.



TECHNICAL SPECIFICATIONS

Max in wood	255 mm
Max cut in pipe	130 mm
Strokes per Minute	0 – 3,000 spm
Stroke Length	30 mm
Input wattage	1200 w
Net weight	3.2 – 3.3 kg
Noise sound pressure	88 dB(A)
Noise sound power	99 dB(A)
Noise K factor	3 dB(A)
Vibration K factor	1.5 m/sec ²
Vibration: Cutting Chipboard	19.5 m/sec ²

USER BENEFITS

- Variable speed trigger control.
- High power
- Joist hook
- Fixed shoe position
- Compact overall length 447mm
- Increased durability achieved by changing the slider holding mechanism.
- Tool-less blade change.
- Lock-on function
- Ergonomic soft grip
- Double Insulation

EAN 0088381891905

[Link zur Produktseite - www.makita.de](http://www.makita.de)



RELATED PRODUCTS

Standard accessories

821621-3

Transport case



Optionales Zubehör

821621-3

Transport case



B-03030

Reciprobblatt HSS Geschränkt



B-05038

Reciprobblatt BIM 152/7-18Z



B-05044

Reciprobblatt BIM 152/6-11Z



B-05153

Reciprobblatt HCS 203/6-10Z



B-55566

Reciprobblatt Rettung



B-55572

Reciprobblatt Rettung



B-55572-10

Reciprobblatt Rettung



B-55588

Reciprobblatt Rettung



B-55588-10

Reciprobblatt Rettung



B-55594

Reciprobblatt Rettung



B-55594-10

Reciprobblatt Rettung



P-04905

Reciprobblatt BIM 150/24Z



P-04911

Reciprobblatt BIM 150/14Z



P-04933

Reciprobblatt BIM 200/18Z

