

Features

- Swiftlock Adjustment System
- Adjusts from 945mm to 1480mm
- Fully adjustable legs independently adjustable
- Durable & lightweight made with aero space grade aluminium
- Anodised armour finish
- Easy to store can be kept in small spaces
- Easy to carry with carry handle
- Platform depth 300mm

RS PRO Fully Adjustable Aluminium Work Platform, 0.48-0.70 m Height

RS Stock No.: 0827585



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

This RS PRO fully adjustable aluminium work platform is designed to provide maximum flexibility, stability, and durability for professional and DIY applications. Featuring a Swiftlock adjustment system, the platform can be quickly and easily adjusted to suit different working heights, allowing operators to work comfortably and efficiently across a wide range of tasks.

The platform is equipped with independently adjustable legs, ensuring excellent stability even on uneven surfaces. Manufactured from high- strength aerospace- grade aluminium, it offers an outstanding balance of strength and lightweight performance. An anodised armour finish enhances resistance to wear and corrosion, making the platform suitable for demanding indoor and outdoor environments.

Designed with portability in mind, the platform folds compactly for easy storage and transportation. An integrated carry handle allows effortless movement between work areas, making this a versatile and dependable solution for maintenance, installation, and trade applications.

General Specifications

Material	Aluminium
Product type	Adjustable Work Platform
Treads	2
Platform Height (m)	0.48-0.70
Approx. Working Height (m)	2.23-2.45
Closed Height (m)	1.04
Width (m)	1.34
Open Depth (m)	1.34-2.02
Weight (kg)	10.2