



Main

Range of product	Altira
Product or component type	Socket-outlet
Device presentation	Mechanism
Number of power socket outlets	2 2P + E French
Outlet standard description	Pin earth
Socket additional information	Shuttered
Colour tint	Polar white (RAL 9003) cover plate

Complementary

Product destination	Fixing frames
Range compatibility	OptiLine 45 OptiLine 70 with Altira adaptor
Ground lug position	Slanted 45° position
Rated current	16 A - 250 V - AC - 50/60 Hz
Number of modules	4 modules
Fixing mode	Clip-in
Connections - terminals	Screwless terminals
Number of cables	4 x 1.5...2.5 mm ² for solid stranded cable(s) 4 x 1.5...2.5 mm ² for rigid cable(s)
Material	PC for mechanism cover
Surface treatment	Untreated
Surface finish	Satin
Product compatibility	Altira fixing frame
Standards	EN 60529 EN 62262 IEC 60884-1 NF C 61-314
Height	45 mm
Width	90 mm
Depth	39 mm
Product weight	0.087 kg

Environment

Ambient air temperature for operation	5...50 °C
Ambient air temperature for storage	-15...60 °C
IK degree of protection	IK02
IP degree of protection	IP20
Environmental characteristic	Acetone Alcohol Ammonia Bleach Liquid soap Oil Petrol UV resistant Window-cleaning fluid Hydrogen peroxide (H2O2)
Environmental health and issues	Halogen free