

4U 19in Steel Vertical Wall Mount Equipment Rack Bracket

Product ID: RK419WALLV



The RK419WALLV 4U Wallmount Rack Bracket offers a versatile storage solution, allowing equipment (Network devices, power strips, patch panels) to be mounted vertically (flush with the wall) to save space. Alternatively, the 4U bracket can be installed under a desk for horizontal installation, making it easy to access installed equipment directly from your workspace. This TAA compliant product adheres to the requirements of the US Federal Trade Agreements Act (TAA), allowing government GSA Schedule purchases.

Perfect for SoHo (small office, home office) environments, the wallmount bracket offers space-saving installation for environments lacking the footprint space for a full size server equipment rack.

Suitable for mounting on virtually any wall/ceiling surface (e.g. drywall), the bracket mounting holes (used to mount to a wall or the desk underside) are positioned at exactly 16in apart, matching standard construction framework.

Constructed to EIA-310 19in rack standards, the wallmount bracket features a sturdy steel design and is backed by StarTech.com's Lifetime Warranty.

Need more storage space? StarTech.com also offers a [1U 19in Wallmount Bracket](#), a [2U 19in Wallmount Bracket](#) and a [3U 19in Wallmount Bracket](#).

Certifications, Reports and Compatibility



Applications

- Mount networking and telecommunication equipment flush against the wall
- Mount KVM switches or workstations under a desk or work bench to free up work space
- Ideal for small and medium businesses needing rack solutions

Features

- 4U Wallmount design
- Equipment can be vertically wall mounted, or horizontally under a desk
- TAA compliant for GSA Schedule purchases
- Arrives fully assembled with cage screws and nuts for mounting equipment
- Wall mounting holes are 16" center to center for greater stability, and mounting to standard wall studs
- Constructed to meet the EIA-310 19" rack standards
- Made from solid steel for durability

Hardware	Warranty	Lifetime
	Frame Type	Open Frame
	Industry Standards	EIA/ECA-310-E
	Mounting Hole Types	Square (For Cage Nut)
	Mounting Rail Profile	L-Shape
	Rack Type	2-Post
	U Height	4U
	Wallmountable	Yes
Performance	Weight Capacity	125.3 lb [56.7 kg]
Special Notes / Requirements	Note	Package includes 1½" screws for mounting to wood surfaces, additional hardware will be required for other materials
Physical Characteristics	Color	Black
	Construction Material	Steel
	Enclosure Type	Steel
Product Measurements	Product Height	7.6 in [19.3 cm]
	Product Length	5.9 in [15.1 cm]
	Product Width	19.8 in [50.4 cm]
	Weight of Product	2.4 lb [1.1 kg]
Packaging Information	Flat Pack (Assembly Required)	No
	Package Height	6.4 in [16.2 cm]
	Package Length	20.4 in [51.9 cm]
	Package Width	8.3 in [21.1 cm]
	Shipping (Package) Weight	3.7 lb [1.7 kg]
What's in the Box	Included in Package	1 - Vertical Wall Mount Bracket
		16 - M5 Cage Nuts
		16 - M5 Screws
		6 - Wood Screws
		1 - Instruction Manual

Product appearance and specifications are subject to change without notice.