

MERKMALE

- Ideal zum Reinigen und Reparieren beschädigter oder korrodierter Gewinde
- HSS-Konstruktion der Teile
- Einfaches und sauberes Schneiden in Metalle
- Kann mit einem Hahnschlüssel oder Elektrowerkzeug verwendet werden
- Jedes Teil ist im praktischen Koffer gekennzeichnet

HSS M12-Spiralkopf- Gewindebohrersatz von RS Pro

RS Best.-Nr. 668-1119



Professionelle Produkte von RS bieten Ihnen hochwertige Teile in allen Produktkategorien. Unsere Produktpalette wurde von

Ingenieuren getestet und bietet eine vergleichbare Qualität wie die führenden Marken, ohne einen Premium-Preis zu zahlen.

Produktbeschreibung

Wir stellen Ihnen die Serie von RS Pro Hand-Gewindebohrersätzen vor. Dieser hochwertige Satz enthält alle wichtigen Geräte und Zubehörteile, die zum erfolgreichen Reinigen oder Schneiden neuer Gewinde an Befestigungselementen, Löchern und vielem mehr erforderlich sind. Das HSS-Material (High-Speed-Stahl) erleichtert das Schneiden härterer Materialien mit Präzision und Effizienz, sodass dieser Satz ideal für professionelle Handwerker oder allgemeine technische und automotive Anwendungen ist.

Allgemeine

Gewindegröße	M12
Typ	Gewindebohrer
Gewindestandard	Metrisch
Inhalt	Gewindebohrer: 3 x M3; M4; M5; M6; M8; M10; M12, runde Matrizen: M3; M4; M5; M6; M8; M10; M12 (25 x 9 mm), Gewindebohrer Schraubenschlüssel: 1-1/2 Zoll, Matrizenhalter: 25 x 9 mm, Schraubendreher
Anzahl der Teile	32
Standardausführung	ISO-metrisch
Anwendungen	Kfz-Anwendungen und -Reparatur, Allgemeine Wartungswerkstätten, Heimwerker, Maschinenreparatur

Mechanische

Werkstoff	HSS
Maximale Gewindebohrergröße	M12
Minimale Gewindebohrergröße	M3



RS STOCK NUMBER	MANUFACTURE PART NO.	DESCRIPTION	CONTENT
6681113	T9705	7PC HSS LEFT HAND TAP SET	ISO HSS Taps as Follows: M3, M4, M5,M6,M8,M10,M12, Left Hand, Metric Coarse,Second Tap Package: Red Metal Box
6681119	T9221	22PC HSS TAP SET	ISO HSS Taps as Follows, 3pcs per each size: M3, M4, M5,M6,M8,M10,M12; metric Coarse 1pc Tap Wrench: No. 1 1/2 (M5-M12, 3/16"-1/2") Package: Red Metal Box
6681125	T9322	32PC HSS TAP AND DIE SET	21pcs DIN352 HSS Taps as Follows, 3pc each size : M3, M4, M5,M6,M8,M10,M12 7pcs DIN 223 HSS Round Dies 25X9mm, without split as Follows: M3, M4, M5,M6,M8,M10,M12 1pc Tap Wrench: No. 1 1/2 1pc Die Holder 25X9mm 1pc Screwdriver Package: Grey Metal Box
6681138	T9323	32PC HSS TAP AND DIE SET	21pcs DIN352 HSS Taps as Follows, 3pc each size : M3, M4, M5,M6,M8,M10,M12 7pcs DIN 223 HSS Round Dies 25X9mm, without split as Follows: M3, M4, M5,M6,M8,M10,M12 1pc Tap Wrench: No. 1 1/2 1pc Die Holder 25X9mm 1pc Screwdriver Package: Grey Blow Mold Case
6681122	T9442	44PC HSS TAP AND DIE SET	21pcs DIN352 HSS Taps as Follows, 3pc each size : M3, M4, M5,M6,M8,M10,M12 7pcs DIN 223 HSS Round Dies, without split as Follows: M3, M4, M5,M6,M8,M10,M12 7pc HSS Drills:2.5,3.3,4.2,5.0,6.8,8.5,10.2mm 2pcs Tap Wrench: No.1, No.2 5pcs Die Holder: No.1, No.2,No.3, No.4, No.5 1pc Screw Pitch 1pc Screwdriver Package: Grey Metal Box
6681129	T9540	54PC HSS TAP AND DIE SET	33pcs DIN352 HSS Taps as Follows, 3pc each size : M3, M4, M5,M6,M8,M10,M12,M14,M16,M18,M20 11pcs DIN 223 HSS Round Dies, without split as Follows: M3, M4, M5,M6,M8,M10,M12,M14,M16,M18,M20 2pcs Tap Wrench: No.1, No.3 6pcs Die Holder: No.1, No.2,No.3, No.4, No.5, No.6 1pc Screw Pitch 1pc Screwdriver Package: Grey Metal Box

RS STOCK NUMBER	MANUFACTURE PART NO.	DESCRIPTION	CONTENT
6681113	T9705	7PC HSS LEFT HAND TAP SET	ISO HSS Taps as Follows: M3, M4, M5,M6,M8,M10,M12, Left Hand, Metric Coarse,Second Tap Package: Red Metal Box
6681119	T9221	22PC HSS TAP SET	ISO HSS Taps as Follows, 3pcs per each size: M3, M4, M5,M6,M8,M10,M12; metric Coarse 1pc Tap Wrench: No.1 1/2 (M5-M12, 3/16"-1/2") Package: Red Metal Box
6681125	T9322	32PC HSS TAP AND DIE SET	21pcs DIN352 HSS Taps as Follows, 3pc each size : M3, M4, M5,M6,M8,M10,M12 7pcs DIN 223 HSS Round Dies 25X9mm, without split as Follows: M3, M4, M5,M6,M8,M10,M12 1pc Tap Wrench: No.1 1/2 1pc Die Holder 25X9mm 1pc Screwdriver Package: Grey Metal Box
6681138	T9323	32PC HSS TAP AND DIE SET	21pcs DIN352 HSS Taps as Follows, 3pc each size : M3, M4, M5,M6,M8,M10,M12 7pcs DIN 223 HSS Round Dies 25X9mm, without split as Follows: M3, M4, M5,M6,M8,M10,M12 1pc Tap Wrench: No.1 1/2 1pc Die Holder 25X9mm 1pc Screwdriver Package: Grey Blow Mold Case
6681122	T9442	44PC HSS TAP AND DIE SET	21pcs DIN352 HSS Taps as Follows, 3pc each size : M3, M4, M5,M6,M8,M10,M12 7pcs DIN 223 HSS Round Dies, without split as Follows: M3, M4, M5,M6,M8,M10,M12 7pc HSS Drills:2.5,3.3,4.2,5.0,6.8,8.5,10.2mm 2pcs Tap Wrench: No.1, No.2 5pcs Die Holder: No.1, No.2,No.3, No.4, No.5 1pc Screw Pitch 1pc Screwdriver Package: Grey Metal Box
6681129	T9540	54PC HSS TAP AND DIE SET	33pcs DIN352 HSS Taps as Follows, 3pc each size : M3, M4, M5,M6,M8,M10,M12,M14,M16,M18,M20 11pcs DIN 223 HSS Round Dies, without split as Follows: M3, M4, M5,M6,M8,M10,M12,M14,M16,M18,M20 2pcs Tap Wrench: No.1, No.3 6pcs Die Holder: No.1, No.2,No.3, No.4, No.5, No.6 1pc Screw Pitch 1pc Screwdriver Package: Grey Metal Box