

Constant Voltage LED Driver 12vdc 39.6 Watt



The RS Pro Range of 39.6watt Constant voltage LED Drivers are housed in a compact light weight high quality IP20 plastic enclosure with covered input & output terminals suitable for general Indoor LED applications

Features:

- Input Voltage 200-240vac
- IP20 Rated
- Low Profile
- Compact Plastic Low Profile enclosure
- 1 Year Warranty



ENGLISH

Specification

Part Number	1766706
Output Voltage Rating	12vdc
Output Current Range	3.33A
Rated Power	40 Watt
Dimensions	159.9 x 57.8 x 18mm
Input Voltage Range	200-240VAC
Input Voltage Frequency	50-60Hz
Inrush Current	<70A
input power	<48W
Efficiency	≥85%
Power Consumption Without Load	<0.5W
Overload Protection	Ta ,0.94-1.06 times of input voltage, 1.6times of rated power
Short Circuit Protection	Ta ,0.94-1.06 times of input voltage
Automatically Restart	Yes
Working Temperature	-20-45C
Relative Humidity	45%-85%
MTBF	30K Hours
EMC emission	EN55015
EMC Immunity	EN6100-3-2, EN61000-3-3, EN61547
Safety Standards	EN61347-1, EN61347-2-13