



PRODUCT-DETAILS

BVND-P132GT-11

CONDFTNG STR PG13 NW12 IP66 CSA BLK



General Information

Extended Product Type:	BVND-P132GT-11
Product ID:	7TAA292150R0188
EAN:	7630030213410
Catalog Description:	CONDFTNG STR PG13 NW12 IP66 CSA BLK
Long Description:	VN Straight Connector for IP66 Static Conduit - Thread PG 13.5, Fits to Conduit Size NW/Metric 12/16, Thread Length 11.0, Color Black
Display Name:	BVND-P132GT-11

Additional Information

Product Main Type:	PMA Flexible Cable Protection
Application:	Use In Railway Vehicle and Heavy Machine Construction
Product Type:	Fittings for Nylon Flexible Conduits

Ordering

EAN: 7630030213410
UPC: 786209951502

Technical

Number of Batteries: 0
Color: Black
Material: Polyamide 6
Size: NW12 , PG13.5 Thread

Environmental

WEEE Category: Product Not in WEEE Scope

Container Information

Package Level 1 Units: 100 EA
Package Level 1 EAN: 7630030213410
Package Level 1 Height: 0 mm
 0 in
Package Level 1 Depth / Length: 0 mm
 0 in
Package Level 1 Width: 0 mm
 0 in

Certificates and Declarations

Data Sheet, Technical Information: BVND-P132GT-11
Instructions and Manuals: BVND-P132GT-11
Declaration of Conformity - CE: 9AKK107680A0674

External Classifications and Standards

ETIM 8: EC001176 - Screw connection for corrugated plastic hose
ETIM 9: EC001176 - Screw connection for corrugated plastic hose
UNSPSC: 39121311

Categories

Products > Low Voltage Products and Systems > Installation Products > Cable Protection, Explosion Proof and Lighting > Flexible Cable Protection Systems

