

FEATURES

- **Sintered Bronze Material:** Offers excellent wear resistance and longevity.
- **Flanged Design:** Provides additional support and stability during operation.
- **Dynamic Load Rating of 14 N/mm²:** Ensures efficient performance under dynamic conditions.
- **Static Load Rating of 50 N/mm²:** Capable of handling significant static loads.
- **0.37 in Bore Size:** Suitable for a wide range of shaft diameters.
- **0.62 in Outside Diameter:** Compatible with standard housing dimensions.
- **3/4 in Width:** Provides ample surface area for load distribution.

RS PRO 0.37 in Flanged Plain Bearing

RS Stock No: 528-914



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

The RS PRO 0.37 in Flanged Plain Bearing is designed for applications requiring reliable rotational movement with minimal friction. Made from high-quality sintered bronze, this bearing is ideal for use in various industrial settings where durability and performance are critical.

General Specifications

Bore Size	0.37 in
Dynamic Load Rating	14 N/mm ²
Product Type	Plain Bearing
Static Load Rating	50 N/mm ²
Sub Type	Flanged

Mechanical Specifications

Material	Sintered Bronze
Outside Diameter	0.62 in
Width	3/4 in

Approvals

Standards/Approvals	ISO 9001:2008, UKAS 001
---------------------	-------------------------

