



ENGLISH

Datasheet

ECP-20 Euro series

20W plug-in power supply

Features



- Input Voltage: 90 – 264Vac
- Output Power: 20W
- No Load power consumption
- UK and European versions available
- Compact and light-weight plastic case
- Protections: short circuit/overload/ overheat
- 1 year warranty
- Dimensions: 70mm x 60mm x 50mm
- Connector: 2.1 x 5.5 x 9.5mm
- Weight: 154g

Part number	Voltage	Rated Current	Voltage range	Line Regulation	Load Regulation	Ripple and Noise	MTBF
726-2867	5V	4A	4.7 ~ 5.3V	± 1%	± 5%	<10%	100,000hrs min. MIL-HDBK – 217F (25°C)
726-2860	7.5V	2.67A	7.1 ~ 7.9V				
726-2864	9V	2.22A	8.5 ~ 9.5V				
726-2873	12V	1.67A	11.4 ~ 12.6V				
726-2876	15V	1.33A	14.25 ~ 15.75V				
726-2870	18V	1.11A	17.1 ~ 18.9V				
726-2889	24V	0.83A	22.8 ~ 25.2V				

Mechanical specification

