



mechanical hygostat Non-adjustable KFR 012 50% RF

Model		
product brand name		SIVACON
product designation		Mechanical hygrostat
design of the switching function		CO contact
General technical data		
mounting type		Clip for 35 mm rail
type of voltage of the operating voltage		AC
Protection class		
protection class IP		IP 20
Product details		
product component digital display		No
Mechanical Design		
fastening method		terminal mounting
mounting position		Vertical
Environmental conditions		
adjustable response value relative humidity		
• initial value		50 %
• full-scale value		50 %
Certificates		
reference code according to EN 61346-2		K
reference code according to IEC 81346-2		K
Approvals Certificates		
General Product Ap- proval	other	Environment



[Confirmation](#)

[Environmental Conformations](#)

Further information

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=8MR2170-3C>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/8MR2170-3C>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=8MR2170-3C

CAX-Online-Generator

<http://www.siemens.com/cax>

last modified:

5/24/2025 

