



Sample photo

Order symbol: PCT 162409
Product nbr: 7022811
Description: Enclosure, PC
Remarks: Clear transparent cover

EAN: 6418074058676
EI. number:
 Finland: 3435414
 Electric No. 8212002937
 Denmark:
 Electric No. Sweden: 7022811

Including: Base with screws for mounting plate/DIN-rail, cover with PUR gasket and stainless steel cover screws.

| Dimensions: | Length | Width | Height | Rating: |
|-------------------------------------|----------------------|-------|--------|--|
| mm: | 244 | 164 | 90 | Ingress Protection (EN 60529): IP66/IP67 |
| inch: | 9.6 | 6.5 | 3.5 | Impact Resistance (EN 62262): IK07/IK08 |
| Materials: | | | | Electrical insulation: Totally insulated |
| Material: | Polycarbonate | | | Halogen free (DIN/VDE 0472, Part 815): 1 |
| Base colour: | RAL 7035 -light grey | | | UV resistance: UL 508 |
| Cover screws material: | Stainless steel | | | Flammability Rating: UL 746C 5V |
| Cover colour: | Clear transparent | | | Glow Wire Test (IEC 695-2-1) °C: 960 |
| Gasket material: | Polyurethane | | | NEMA Class: NEMA 1, 4, 4X, 12, 13 |
| Temperatures: | | | | Certificates: |
| Temperature °C (short term): | -40 ... 120 °C | | | SGS Fimko |
| Temperature °C (continuous): | -40 ... 80 °C | | | Gost R |
| Temperature °F (short term): | -40 ... 250 °F | | | |
| Temperature °F (continuous): | -40 ... 175 °F | | | |

EURONORD PC/ABS 244x164x90-120

