


Electronic Hour Meter/Miniature DC Hour Meter T33 Series



T33BM736DC, 4.5-35 VDC

Miniature Hour Meter with Low Power Consumption. Series T33 miniature hour meters are quartz crystal oscillator controlled impulse counters. They are ideal for battery operations and use on electronic PC Boards; applications where space is limited.

Features


- Quartz accuracy
- Shock resistant/High reliability
- Low power consumption
- Enhanced readability
- Easy installation
- Waterproof versions available

Specifications

Display:	99999.99
Figures:	White on black (hours) Red on black (decimals)
Figure Size:	0.118" high x 0.039" wide 0.158" high w/ magnifying window
Voltage:	4.5-35 VDC \pm 10%
Average Power Consumption:	82 mW (5 VDC) 135 mW (12 VDC) 135 mW (24 VDC)
Operating Temperature:	-10°C to 60°C
Mounting:	Panel and PCB Mount (other variation available)
Termination:	Leads or pins
Weight:	0.7 oz.


T33 Series

Panel Mount




DIMENSIONS [] ARE IN MILIMETERS..

PCB Mount



PCB Mount



2013 ENM Co.®

LIMITED WARRANTY

ENM Company resettable electromechanical counters are warranted to the consumer to be free from defects in material and workmanship for a period of 3 years or 10,000 hours. All ENM products which fall within the warranty period due to defects in material or workmanship will be repaired or replaced, at ENM's option, without charge to the consumer when returned with proof of purchase to any authorized ENM dealer in the United States, transportation charges prepaid, provided there is no evidence of improper installation, tampering, or other abuse. All implied warranties, including any implied warranty of merchantability or fitness for a particular purpose, shall be limited in duration to the express warranty period specified above. ENM disclaims any liability for consequential damages due to breach of any written or implied warranty on its products. Datasheet information subject to change.