

ACTIVARMR™

47-403

Ideal alternative to PVC and light leather gloves

Previously known as: Nitratough™ N250Y



Oil



Medium Duty

Comfortable and flexible abrasion-resistant gloves, providing outstanding oil repellence

- **Specialized protection:** ActivArm® 47-403 abrasion-resistant gloves feature nitrile coating, which ensures outstanding oil repellence on the palm and back of the hand
- **Enhanced comfort:** These safety gloves feature a cotton lining, providing wearers with optimum comfort and flexibility as well as excellent dexterity
- **Added comfort:** ActivArm® 47-403 protective gloves also possess safety cuffs and an elasticated knitwrist, resulting in a reliable and snug fit



Industries

- Agriculture
- Automotive
- Maintenance
- Metal fabrication

Applications

- Assembly and finishing
- General maintenance
- Metal Fabrication
- Quality control

ACTIVARMR™

47-403

Ideal alternative to PVC and light leather gloves

Previously known as: Nitratough™ N250Y

Key Features

- **Nitrile coating:** Superb abrasion and puncture resistance
- **Cotton lining:** Optimal comfort and flexibility
- **Elasticated knitwrist:** A snug fit assured

Performance Standards & Regulatory Compliance

EN388: 2016



3111A

Specifications

BRAND STYLE	DESCRIPTION	Gauge	SIZE	LENGTH	COATING COLOR	PACKAGE
ActivArmr® 47-403	Finishing: Fully Coated Coating Material: Nitrile Liner Material: Cotton Cuff Style: Safety Cuff	N/A	10, 11, 7, 8, 9	260mm	Yellow	12 pairs/bag, 12 bags/carton

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306,
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 900
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Canada

Ansell Canada
105 Lauder
Cowansville, QC J2K 2K8
Canada
T: +1 800 363 8340
F: +1 800 267 3551

Australia

Ansell Limited
Level 3, 678 Victoria Street,
Richmond, Vic, 3121
Australia
T: +61 1800 337 041
F: +61 1800 803 578

Asia Pacific Region

Ansell Global Trading Center
(Malaysia) Sdn Bhd
Prima 6, Prima Avenue
Block 3512, Jalan Teknokrat 6
T: +603 8310 6688
F: +603 8310 6699

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: www.ansell.com/patentmarking © 2025 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

