

95 32 340 SR

ACSR Cable Cutter (ratchet action)

for cables with a steel core



- Handy. Compact. Sturdy.
- Extremely robust design.
- Cuts through aluminium conductor cable with steel core up to a diameter of 32 mm in one or two-handed operation
- Cutters with precision cut and induction hardened cutting edge
- Two-stage ratchet drive for easy cutting
- Less physical effort due to very high transmission ratio
- Fixed handle with support area for putting down the pliers when cutting
- Locking mechanism for transporting with safely closed handles
- Special high grade tool steel, multi stage oil-hardened



| | |
|---------------------------|----------------------------|
| Article No. | 95 32 340 SR |
| EAN | 4003773078579 |
| Tool | burnished |
| Handles | with multi-component grips |
| Diameter mm | 32 |
| MCM | 477 |
| Inch diameter Inch | 1 1/4 |
| Length mm | 340 |
| Net weight g | 1300 |



The strong "flange" on the handle can be used as a practical support surface when cutting larger diameters



Enormous power with a weight of just 1300 g



The outside of these cables consists of light, highly conductive aluminium wire, and the core of extremely non-stretch galvanised steel wires

technical change and errors excepted

Spare Parts

| Article No. | EAN | |
|--------------|---------------|--|
| 95 39 340 01 | 4003773078609 | Pivot cutter repair kit for 95 32 340 SR |