

# M18 HKP-201C

## M18™ FORCE LOGIC™ HYDRAULIC KNOCKOUT PUNCH

- FORCE LOGIC™ hydraulic knockout punch is the most compact and lightweight tool on the market with 60 kN of force
- The easiest way to punch - for fast, accurate, round, and burr free holes
- Highest accuracy due to industry's finest exact alignment system for dies
- Best balanced tool and easiest control due to one hand operation
- Quick connector allows easy set-up of punch and die without carrying the weight of the tool
- Tool punches up to 100 mm holes into 3.0 mm mild steel or 2.5 mm stainless steel
- Compatible with most common punches and dies available on market
- Easiest, less strenuous and nonexpendable way of making holes into sheet metal
- On board fuel gauge and LED light
- Brushless motor, REDLITHIUM™ battery pack and REDLINK™ electronic deliver power, run time and durability
- Flexible battery system: works with all MILWAUKEE® M18™ batteries



### REDLITHIUM™

Punching force (kN)	60
Max. punching diameter (mm)	100
Max. material thickness (mm)	2.5 in stainless and 3.0 in mild steel
Standard equipment	11.1mm (7/16") draw stud, 19mm (¾") draw stud, quick connector, ball pull, adaptor
Kit included	1 x M18 B2 Battery pack, M12-18 C Charger, Kitbox
Article Number	4933451202