



FILE NO:

DESCRIPTION CONTROL			
REV	DESC	DATE	APP
R2	R2	2012-4-23	



CUSTOMER P/N	L±T	M	TIE	PE BAG:L*W*0.06MM	Q'TY
7587428	2000±50	2.0	120*1	PE BAG:6*8*0.06MM	A/R
7587425	3000±50	3.0	150*1	PE BAG:7*10*0.06MM	A/R



*	390	LABEL:75874XX*45*25MM*	R2	1	PCS
*	390	TIE-A/BE		***	MM
*	390	CARTON:46*30*25CM		A/R	PCS
*	390	PE BAG:30*28*0.08MM		A/R	PCS
*	390	PE BAG:L*W*0.06MM		1	PCS
	370	JUMP-WIRE-24#-UL1007		25*1	MM
	6	240010100034 SRW-E31.5/BE02		4	PCS
	5	120010000006 PVC-BE02/50		51	G
	4	220020000001 PVC-IN		12.6	G
	3	100-2510110010N-C CDS-25P<BK>		1	PCS
	2	100-0920110010-C CDS-09S<BK>		1	PCS
	1	1201605502002X NON-UL,26AWG,5C+AD,BE02,DD:5.0		L	M
NO	NO	DESCRIPTION		QTY	UNIT


RoHS COMPLIANT



OUTER MOLDING	IDB9-1505	IDB 2513	
INNER MOLDING	IDB9-1507	IDB 2514	

PIN ASSIGNMENT

P1	P2
1	8
2	2
3	3
5	7
6+8	20
S	S



ITEM:	7587428& 7587425	REV	R2
DRAW, BY:	向三茶	SCALE:	NONE
CHECK, BY:		DATE:	2011.06.14
APP, BY:		CUSTOMER:	C331<RS>
		CUSTOMER P/N:	75874XX R2

ALL DIMENSIONS IN mm