

Hot air tool - Professional Line

PRO HM 2620 E

Set for tarpaulins & groundsheets
EAN 4007841 089542
Article number 089542



7

series 7

2300 W

2300 W Output

Display

Display (LCD)



50 – 700°C



stepless adjustable



150 – 500 l/min.



Suitable for screwable
nozzles



CE



VDE

Function description

The flagship comes with accessories for welding tarpaulins. Hot air tool HM 2620 E, including feed roller, 40x2mm flat angled nozzle and 20x2 flat angled nozzle. 2300 W, digital temperature adjustment by joystick from 50 – 700 °C. Airflow control from 150 – 500 l/min. Features LCD display and residual heat indicator. Brushless motor, integrated fine dust filter, suitable for use on construction sites.

Technical specifications

Temperature	50 – 700 °C
Airflow rate	150 – 500 l/min
Temperature setting	in 10°C steps by joystick
Settings made via	joystick
Temperature display	LCD display
Airflow control	Continuous
Programming function	Yes
Residual heat indicator	Yes
Cool function	Yes
Motor, type	Brushless
Heating element	Ceramic heating element
Mains power supply	220 – 230 V / 50 – 60 Hz
Function, hanger	No
Function, life expectancy, motor	10000 h
Function, life expectancy, heating element	800 h

Replaceable heating element	Yes
Restart protection	Yes
Fine dust filter	Yes
Thermal cut-out	Yes
Thermostat	Yes
Cord length	3 m
Dimensions (L x W x H)	358 x 91 x 95 mm
PU1, net weight	1,53 kg
Manufacturer's Warranty	1 year
PU1, EAN	4007841089542
Scope of delivery	incl. silicone feed roller, 40x2mm flat angled nozzle, 20x2 flat angled nozzle
Power plug	Typ E+F
Output	2300 W
Product category	Hot air tool

<https://www.steinel.de>

Subject to technical modifications

03.2025 Page 1 from 2

PRO HM 2620 E

Set for tarpaulins & groundsheets
EAN 4007841 089542
Article number 089542



Accessories

EAN 4007841 092313	Round nozzle
EAN 4007841 009076	Round nozzle
EAN 4007841 011871	Soldering reflector nozzle
EAN 4007841 007812	Flat angled nozzle 20x2 mm, 100°
EAN 4007841 092115	Flat angled nozzle 20x2 mm - angled
EAN 4007841 092016	Flat angled nozzle 40x2 mm
EAN 4007841 009083	Flat nozzle 40x2 mm perforated
EAN 4007841 084967	Pressure roller Silicone Ø 35 mm
EAN 4007841 010423	Tarpaulin shears
EAN 4007841 009090	Flat nozzle 60x2 mm for bitumen
EAN 4007841 010409	Sieve reflector nozzle 50 x 35 mm
EAN 4007841 011857	Reflector nozzle 20mm
EAN 4007841 034986	Fillet testing device
EAN 4007841 092214	Round nozzle
EAN 4007841 011765	Fast welding nozzle 4mm narrow - for 5mm rd. noz.
EAN 4007841 011840	Fast welding nozzle 5mm narrow - for 5mm rd. noz.
EAN 4007841 010287	Fast welding nozzle 5mm - for 10mm rd. noz.