



PW3 HOLSTER WORK TROUSERS

DESCRIPTION

Rugged trouser made from Kingsmill polyester/cotton 300g fabric with a modern fit and adjustable leg length. Packed full of features to offer superb function and performance including; top loading pre-shaped knee pad pockets, triple stitched seams, crotch gusset to reduce stress and prevent seam failure and a side leg cargo pocket. Pockets have oxford reinforcement for extra durability.

COMPOSITION

-  Titanmill Plus: 65% Polyester, 35% Cotton, 300g
-  100% Polyester, 600D Oxford, PU Coated, 210g
-  Navy/Black 28-48

FEATURES

- Durable polycotton fabric for high performance and maximum wearer comfort
- Reinforced panels in high wear areas for maximum durability
- Reflective piping for increased visibility
- Top-loading knee pad pockets for quick and easy access
- Swing away tool pockets
- 12 Pockets for ample storage
- 2 Side pockets
- 2 back pockets with one open and one featuring a flap
- 1 Thigh pocket with zip closure
- 1 Cargo pocket
- 1 Rule pocket
- 1 Pen pocket

STANDARDS

EN 14404: 2004 + A1: 2010 Type 2 Level 0 (When used in combination with S156)

COLOUR / SIZES

SKU	COLOUR	SIZE RANGE
T602NBR	NAVY/BLACK	28-14

FEATURES



DETACHABLE ID POCKET
ID card holder for ID card display



MACHINE WASHABLE AT 60°C
Reusable and machine washable at 60 degrees



UPF 40+
40+ UPF rated fabric to block 98% of UV rays



PERFORMANCE WORKWEAR
PW3™ contemporary workwear blends sports and lifestyle trends with function, a modern fit and improved comfort.

GET THE COLLECTION

TECHINICAL INFORMATION



OEKO-TEX certification
13.HCN.29764

- Wash garment inside out
- Wash garment inside out and fully fastened
- Wash with similar colours
- Wash dark colours separately

Item	Colour Fit	Len (cm)	Wid (cm)	Hgt (cm)	Weight (Kg)	Cubic (m³)	EAN13	GTIN/DUN14
T602NBR28	Navy/Black	65	45	36	.960	5850.000	5036108310630	15036108799197
T602NBR30	Navy/Black	65	45	36	1.040	5850.000	5036108310647	15036108799203
T602NBR32	Navy/Black	65	45	36	1.008	5850.000	5036108310654	15036108799210
T602NBR33	Navy/Black	65	45	36	1.050	5850.000	5036108310661	15036108799227
T602NBR34	Navy/Black	65	45	36	1.080	5850.000	5036108310678	15036108799234
T602NBR36	Navy/Black	65	45	36	1.100	5850.000	5036108310685	15036108799241
T602NBR38	Navy/Black	65	45	36	1.130	5850.000	5036108310692	15036108799258
T602NBR40	Navy/Black	65	45	36	1.080	5850.000	5036108310708	15036108799265
T602NBR41	Navy/Black	65	45	36	1.150	5850.000	5036108310715	15036108799272
T602NBR42	Navy/Black	65	45	36	1.160	5850.000	5036108310722	15036108799289
T602NBR44	Navy/Black	65	45	36	1.170	5850.000	5036108310739	15036108799296
T602NBR46	Navy/Black	65	45	36	1.200	5850.000	5036108310746	15036108799302
T602NBR48	Navy/Black	65	45	36	1.180	5850.000	5036108310753	15036108799319