



Product data sheet

Power tools for trade & industry

Screwdriver

PRO GSR 12V-32 FC



Bosch Professional's first 12V FlexiClick drill driver with Advanced KickBack Control

The most important data

Battery voltage	12.0 V
Torque, max. (hard/soft)	32 / 21 Nm
Max. screw diameter	8 mm

Part Number 0 601 9N7 102

Technical data

Technical data

Torque, max. (hard/soft)	32 / 21 Nm
Battery voltage	12.0 V
Weight excl. battery	0.6 kg
Packaging dimensions (width x length x height)	360 x 444 x 117 mm

Screw diameter

Max. screw diameter	8 mm
---------------------	------

**BOSCH**

Invented for life

Product data sheet

Power tools for trade & industry

Advantages:

- High user protection thanks to Advanced KickBack Control, which minimises the risk of injury
- Versatile thanks to easy-to-change FlexiClick attachments that save time and space
- Convenient working even in tightest spaces and hard-to-reach spots due to highly compact design
- Unique: this 12V drill driver can be transformed into an SDS plus rotary hammer by attaching the PRO GFA 12-H hammer attachment
- Highest precision even when working close to edges and walls or around corners thanks to excenter and right angle attachment

**HEAVY
DUTY****PROFESSIONAL
12V
SYSTEM**

You can find more information about the deviations in the following link: <https://www.bosch-professional.com/gb/en/wac/>

