

# COAST

## XP6R PURE BEAM FOCUSING TORCH



**DUAL POWER**

ZITHION-X™ Rechargeable — Also works with a CR123 Lithium battery



SLIDE FOCUS & BEAM LOCK

PURE BEAM FOCUS  
FLAMMABLE

ANTI ROLL TAIL CAP

THREE-MODE LIGHT OUTPUT



**400**  
LOWERS BRIGHT

**8**  
HOUR RUNTIME

DUST RESISTANT WEATHER PROOF  
IP54

POWER SOURCES:  
Li ION OR LITHIUM  
CR123

COAST TRUSTED TOUGH™

FIVE YEAR WARRANTY

# XP6R



### An Ultra-Compact Pocket Flashlight in COAST's NEW Durable "Extreme Performance" Line of Portable Lighting Solutions

Big on light, small on size. The COAST XP6R torch delivers brightest-in-class light with a new, more rugged look consistent with COAST's new line of XP (Extreme Performance) torches. The XP6R is 3.5 inches in length and packs a punch, with 400 lumens of maximum brightness. The torch features three light output levels, and multi-beam capability powered by a COAST ZITHION-X™ rechargeable battery.

This torch is equipped with COAST's Dual Power™ technology, meaning the torch is also compatible with a CR123 disposable lithium battery (sold separately).

This pocket-sized handheld torch features patented slide-focusing optical technology that shines clean flood light and piercing spot light with seamless transitions between.

- 400 lumens with rechargeable battery cell
- Length: 3.55 in. / 9.04 cm
- ZITHION-X™ rechargeable battery (included), or a CR123 battery (sold separately)

