



Model No. 8433EURD

1,8m long x 10mm diameter Python™ adjustable locking cable; black and yellow

Best Used For:



Fences



Grills & Lawnmowers



Residential Gates & Fences



Tools, Job Boxes & Gang Boxes

Security Level:



Basic to medium security:

Generally recommended for indoor general purpose

Overview & Features

Product Features

- Patented locking mechanism holds the cable tight at any position from 30 cm to 1,8 m for infinite locking positions
- Interchangeable cables for application flexibility
- 100% steel braided cable
- Weather tough and rust resistant lock body and cable
- Vinyl sleeve and lock body bumper prevents scratching
- Strap holds excess cable for compact storage

Product Details

The Master Lock No. 8433EURD Python™ Adjustable Locking Cable is 1,8m long and features 10mm diameter braided steel for maximum strength and flexibility. The protective vinyl coating protects against scratches. The integrated pin tumbler keyed locking mechanism provides superior pick resistance. The rust resistant lock and vinyl coated cable provide superior weather and scratch resistance. The Limited Lifetime Warranty provides peace of mind from a brand you can trust.

Product Specifications

Product Number	8433EURD
Cable/Chain Length	1.8 m
Outside Diameter of Cable/Chain	10 mm
Colour	Black
Description	Keyed Different
Master Carton Qty	4

Master Lock Europe S.A.S.

10 avenue de l'arche - Le Colisée Gardens, bâtiment A - 92 400 Courbevoie - La Défense - France
O: +33-1-41437200 | F: +33-1-41437204
www.masterlock.eu