

### Model 1000 3/4", N.m/lbf.ft



These Wrenches were designed as an extension to our 'Professional' range of Torque Wrenches, Models 60 - 330 and so have the same high quality and accuracy.

**Part number:** 14002

**EAN Bar Code:** -

**NATO number:** -

**Accuracy:** +/- 3%

**Operates between:**

220.0 - 750.0 lbf-ft

300.0 - 1000.0 N-m

Model 1000



## TECHNICAL SPECIFICATIONS

- Length: 1250 mm
- Square Size: 3/4"
- Torque Radius: 1098 mm
- Weight: 5.8 Kg
- Ratchet Teeth: 60
- Ratchet Type: push-through
- Length (inc. Ext. Handle): 1750 mm

## FEATURES

- Accuracy of +/-3% of reading.
- Non length dependent. Extension handle can be used to reduce operator effort (handle supplied as standard with Model 800, 1000 and 1500).
- Positive 'click' can be heard seen and felt.
- Low weight - Model 1000 just 5.8 kg.
- Long scale length in N-m and lbf-ft allows error free setting.
- Fine 60 tooth ratchet allows the wrench to be used in confined areas.
- Supplied in a high quality blow moulded plastic case, with space provided for accessories such as sockets.