


Technical data sheet

Article number:
118-00173

T50MOS



Product Group	Cable ties made from post-industrial recycled polyamide 6.6
Product Family	OS-Series in PA66HIRHS(REC) black
Material	Polyamide 6.6 recycled, high impact modified, heat stabilised (PA66HIRHS(REC))
Colour	Black (BK)
Application Tool	MK3PNSP2, EVOcut, MK7P, MK10-SB, MK20, EVO7SP, EVO7i, EVO7iSP
Bundle Ø max.	66.0 mm
Bundle Ø min.	1.6 mm
Halogen-free	Yes
Height (H)	1.3 mm
Length (L)	245 mm
Min.Tensile Strength	225 N
Operating Temperature	-40 °C to +105 °C
Package Content packed in	bag
Pack Cont.	100 pcs.
Releasable Closure (Yes/No)	No
Thickness (T)	1.3 mm
Toothing (Serration)	Outside Serrated
Variant	Outside Serrated
Weight/Unit	0.001634 kg
Width (W)	4.6 mm

HF ✓

RoHS ✓