

PRODUCT-DETAILS

GRNY-040-9-C

GROMMETING EXTD .04IN NAT NYL 100FT



General Information

Extended Product Type	GRNY-040-9-C
Product ID	7TAG009750R0018
EAN	5414363023470
Catalog Description	GROMMETING EXTD .04IN NAT NYL 100FT
Long Description	Extruded Grommeting, Natural Nylon 6.6 for Temperatures up to 85 Degrees Celsius (185 F), Height of 4.83mm (0.19 Inches), Width of 3.17mm (0.125 Inches), Thickness 1.02mm (0.04 Inches), Width Maximum Panel Thickness of 1.02mm (0.04 Inches), 30.48m (100 Foot) Reel

Ordering

EAN	5414363023470
UPC	728494119519

Dimensions

Product Net Depth / Length	100 ft 30.48 m
----------------------------	-------------------

Container Information

Package Level 1 Units	1 piece
Package Level 1 Width	12 in 305 mm

Package Level 1 Height	1 in 25 mm
Package Level 1 Depth / Length	15 in 381 mm
Package Level 2 Units	20 piece
Package Level 2 Width	13 in 330 mm
Package Level 2 Height	13.5 in 343 mm
Package Level 2 Depth / Length	18.25 in 464 mm

Additional Information

Brand / Label	Ty-Rap
Color	Natural
Effective Date	19960215
Material	Nylon/Polyamide 6.6
Number of Batteries	0
Panel Thickness	0.04 in 1.02 mm
Product Name	NYLON GROMMETING
Product Type	Grommeting
Special Functions	Used to line panel edges and knockouts where the chafing of wires is a concern

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	GRNY-040-9-C
Instructions and Manuals	GRNY-040-9-C

Classifications

ETIM 6	EC002604 - Cable bundle hose
ETIM 7	EC002604 - Cable bundle hose
UNSPSC	39131603
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	5393 >> Grommet edging

Categories

Low Voltage Products and Systems → Installation Products → Wire Management and Connectivity → Cable Ties

