



Features

-



Product Overview

Product name	SYLPIPE L300 530LM 3CCT IP20
Technology	LED
Cap/Base	N/A
Housing	PC Polycarbonate
General application	Residential & Consumer, Retail
ETIM Class	EC000109
Fixture luminous flux (lm)	530
Luminaire efficacy (lm/W)	133
Correlated colour temperature (k)	4000
Light colour	Warm White or Neutral White or Daylight
CRI (Ra)	80
Photobiological Risk Group	RG1
Total power consumption (W)	4
Electrical protection	Class II
Dimmable	No
IP rating	IP20
IK rating	IK03
Product EAN number	5410288902401
Warranty	3 years
Dimming method	N/A



SYLPIPE L300 530LM 3CCT IP20
0090240

Data table

GENERAL DATA

Product name	SYLPIPE L300 530LM 3CCT IP20
Technology	LED
Cap/Base	N/A
Housing	PC Polycarbonate
General application	Residential & Consumer, Retail
ETIM Class	EC000109
Warranty	3 years

OPTICAL DATA

Fixture luminous flux (lm)	530
Luminaire efficacy (lm/W)	133
Correlated colour temperature (k)	4000
Light colour	Warm White or Neutral White or Daylight
CRI (Ra)	80
Photobiological Risk Group	RG1

ELECTRICAL DATA

Total power consumption (W)	4
Primary Supply/Product voltage - min (V)	220.0
Primary Supply/Product voltage - max (V)	240.0
Lamp power factor	0.5
Electrical protection	Class II
Control gear required	No
Dimmable	No
Dimming method	N/A
Inrush Current (A)	5.5
Inrush Duration (µs)	100
Energy Efficiency Class (A->G) of contained light source	C
Nominal Frequency (Hz)	50/60Hz

SYLPIPE L300 530LM 3CCT IP20 0090240

Connectable conductor cross section - Max (mm ²)	0.75
---	------

LIFETIME DATA

Lifespan L70 B50	30000
------------------	-------

PHYSICAL DATA

IP rating	IP20
-----------	------

IK rating	IK03
-----------	------

Nominal Product Length (mm)	294
-----------------------------	-----

Nominal Product Width (mm)	24
----------------------------	----

Nominal Product Height (mm)	35
-----------------------------	----

Weight (kg)	0.065
-------------	-------

PACKAGING

Product EAN number	5410288902401
--------------------	---------------

Packaging single length / height (cm)	48.0
---------------------------------------	------

Packaging single width (cm)	4.0
-----------------------------	-----

Packaging single depth (cm)	3.2
-----------------------------	-----

DUN14 (inner)	15410288902408
---------------	----------------

Units per outer package	40
-------------------------	----

Packaging outer length / height (cm)	49.5
--------------------------------------	------

Packaging outer width (cm)	22.5
----------------------------	------

Packaging outer depth (cm)	28.0
----------------------------	------

SAFETY DATA

Special purpose lamp	No
----------------------	----

Dry applications use only	No
---------------------------	----

Suitable for household illumination	No
-------------------------------------	----