

Datasheet

RS Pro Zinc Plated Steel Adjustable Height Mount 68mm Rubber 95mm 35mm 125mm 150kg 100mm M10 3.5°

RS Stock No: **283-1749**



Product Details

RS Pro zinc plated steel adjustable height mount is designed for use in applications that impose strict safety and reliability demands on the installation and damping of light and medium duty machinery. The zinc plated steel machine mount is suitable for use in less demanding environments. The built in levelling bolt means the mount can be adjusted within a large range with considerable accuracy, allowing a 7° inclination while still maintaining stability.

Features and Benefits

- Long bolt offers height adjustment
- Compensates with up to 7° swivel
- 150 kg static load capacity
- Rubber foot



ENGLISH

Specifications:

Base Material	Zinc Plated Steel
Diameter	68 mm
Foot Material	Rubber
Maximum Adjustment Height	95 mm
Minimum Adjustment Height	35 mm
Overall Height	125 mm
Static Load Capacity	150 kg
Thread Length	100 mm
Thread Size	M10
Tilt Angle	3.5°