


Leiterquerschnitt/ *wire gauge* : 0,14-0,37mm<sup>2</sup> /AWG26-22  
 Oberfläche/ *surface* : Gold Tec (NiP+Au)

 All Dimensions in mm Original Size DIN A 4		Techn. Character.			Nicht tolerierte Masse/ <i>Free size tolerances</i>		
			Dat.	Name	Massstab/ <i>Scale</i>  5:1	Han E-Kontaktbuchse-c <i>Han E-female contact</i>	
			Detail.	14.05.04 Ste			
			Insp.	KR			
			Stand.				
411022			HARTING Electric GmbH & Co. KG D-32339 Espelkamp			TB 09 33 000 6427	Blatt/ <i>page</i> /
Mod.	Dat.	Name	