

## Ha-MK4 MZ4-1M



Image is for illustration purposes only. Please refer to product description.

Part number	72 MN F4M NM40 10
Specification	Ha-MK4 MZ4-1M
HARTING eCatalogue	<a href="https://harting.com/72MNF4MNM4010">https://harting.com/72MNF4MNM4010</a>

### Identification

Category	System cabling
Series	Circular connectors 7/8"
Element	Cable assemblies
Specification	Pre-assembled on both sides
Connector 1	7/8" Male Straight
Connector 2	7/8" Female Straight
Type of cable	Copper cable (round)

### Version

Cable length	1 m
Number of cores	4
Core structure	4x AWG 16

### Technical characteristics

Limiting temperature	-35 ... +75 °C
----------------------	----------------

### Material properties

Material (cable)	PVC
Colour (cable)	Black



**Pushing Performance**  
Since 1945

## Specifications and approvals

Approvals	CE
-----------	----

## Commercial data

Packaging size	1
Country of origin	China
European customs tariff number	85444290
GTIN	5713140261778
eCl@ss	27060390 Ready-made data cable (unspecified)
ETIM	EC002599
UNSPSC 24.0	26121600