

## SPECIAL – TWEEZERS FOR THE SMD – TECHNIQUE

high precision tweezers from special steel  
stainless - matt finish - anti-magnetic - acid-resisting

**5-060 6-piece set ESD-Tweezers for the SMD-Technique**  
with black **ESD-coating**,  
in a wallet made from **conductive** material

The tweezers have been tested with good results adequate to DIN EN 61340-5-1, 61340-2-1, 61340-2-3 for work in ESD-protected areas.

Weight: 155 g

| No. | Description of individual tools |
|-----|---------------------------------|
|-----|---------------------------------|

- |          |   |
|----------|---|
| 5-049-13 | <b>SMD-tweezers</b> , straight, very sharply pointed, 110 mm      |
| 5-055-13 | <b>SMD-tweezers</b> , sickle-shaped, very sharply pointed, 120 mm |
| 5-059-13 | <b>SMD-tweezers</b> , flat, rounded tips, 2 mm width, 120 mm      |
| 5-067-13 | <b>SMD-tweezers</b> , tip 45° angled, 2,0 mm width, 120 mm        |
| 5-068-13 | <b>SMD-tweezers</b> , tip angled, 1,6 mm, 120 mm                  |
| 5-078-13 | <b>SMD-tweezers</b> , tapering, chisel, 1,0 mm width, 130 mm      |



**5-050 6-piece set of special tweezers for the SMD-technique**  
matt finish - non-reflective -

Weight: 135 g

| No. | Description of individual tools |
|-----|---------------------------------|
|-----|---------------------------------|

- |       |  |
|-------|--|
| 5-051 | <b>SMD-tweezers</b> , straight pointed, 115 mm                           |
| 5-052 | <b>SMD-tweezers</b> , bent, very sharply pointed, 110 mm                 |
| 5-054 | <b>SMD-tweezers</b> , sickle-shaped curved, very sharply pointed, 120 mm |
| 5-058 | <b>SMD-tweezers</b> , crossed, bent, pointed, 120 mm                     |
| 5-061 | <b>SMD-tweezers</b> , bent, flat tips 2 mm wide, 115 mm                  |
| 5-062 | <b>SMD-tweezers</b> , bent, flat tips, with gripping cavity, 115 mm      |

