




Part Number : [982670230](#)

Product Description : 1.00mm Pitch Premo-Flex FFC Jumper, Opposite Side Contacts (Type D), 102.00mm Cable Length, Tin (Sn) Plating, 8 Circuits

Series Number : 98267

Status : Active

Product Category : Flat-Flexible Cable (FFC)



Documents & Resources

Drawings

[982670230 sd.pdf](#)

[STEP AP242](#)

[SOLIDWORKS](#)


[Creo](#)

Specifications

[PS-98267-001-001.pdf](#)

Product Environment Compliance

Compliance

| | |
|--------------------|---|
| GADSL/IMDS | Not Relevant |
| China RoHS | per SJ/T 11365-2006  |
| EU ELV | Not Relevant |
| Low-Halogen Status | Not Low-Halogen per IEC 61249-2-21 |
| REACH SVHC | Not Contained per D(2023)8585-DC (23 Jan 2024) |
| EU RoHS | Compliant per EU 2015/863 |

[Compliance Statements](#)

- EU RoHS
- REACH SVHC
- Low-Halogen

[Industry Documents](#)

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

| | |
|--------------|--|
| Status | Active |
| Category | Flat-Flexible Cable (FFC) |
| Series | 98267 |
| Description | 1.00mm Pitch Premo-Flex FFC Jumper, Opposite Side Contacts (Type D), 102.00mm Cable Length, Tin (Sn) Plating, 8 Circuits |
| Comments | Contacts on opposite sides, Type D |
| Product Name | Premo-Flex FFC Jumper |
| UPC | 756054770504 |

Electrical

| | |
|-------------------------------|--------|
| Current - Maximum per Contact | 1.2A |
| Voltage - Maximum | 60V AC |

Physical

| | |
|---------------------------|-------------------|
| Cable Length | 102.00mm |
| Circuits (Loaded) | 8 |
| Contact Layout Type | D (opposite side) |
| Design Feature | Extra-Flexible |
| Material - Plating Mating | Tin |
| Net Weight | 0.620/g |
| Packaging Type | Bag |
| Pitch - Mating Interface | 1.00mm |

| | |
|-------------------------------|-----------------|
| Temperature Range - Operating | -40° to +105°C |
| Termination Style | FFC Connector |
| Wire/Cable Type | Flat Flex Cable |
| Wire Size (AWG) | N/A |

Mates With / Use With

Mates with Part(s)

| Description | Part Number |
|--|----------------------------------|
| Easy-On FFC/FPC Connector, 1.00mm Pitch, Slider Series, Right-Angle, Bottom Contact, 3.00mm Height, 8 Circuits, Tin-Bismuth Plating | <u>522710879</u> |
| Easy-On FFC/FPC Connector, 1.00mm Pitch, Slider Series, Vertical, 5.75mm Height, 8 Circuits, Tin-Bismuth Plating | <u>526100871</u> |
| Easy-On FFC/FPC Connector, 1.00mm Pitch, Slider Series, Vertical, 5.75mm Height, 8 Circuits, Tin-Bismuth Plating, with Pick-and-Place Tape | <u>526100875</u> |
| 1.00mm Pitch Easy-On FFC/FPC Connector, Surface Mount, Vertical, Non-ZIF, Tin (Sn) Plating, 8 Circuits | <u>528080870</u> |
| 1.00mm Pitch Easy-On FFC/FPC Connector, Surface Mount, Vertical, Non-ZIF, Tin (Sn) Plating, with Pick-and-Place Polyimide Tape, 8 Circuits | <u>528080871</u> |
| Easy-On FFC/FPC Connector, 1.00mm Pitch, Slider Series, Right-Angle, Top Contact, 2.70mm Height, 8 Circuits, Tin-Bismuth Plating | <u>522070885</u> |
| 1.00mm Pitch Easy-On FFC/FPC Connector, Surface Mount, Right-Angle, Non-ZIF, Top Contact Style, 8 Circuits | <u>527930870</u> |

| | |
|--|------------------|
| 1.00mm Pitch Easy-On FFC/FPC Connector, Vertical, Surface Mount Compatible, Non-ZIF, Kinked PC Tails, 8 Circuits | <u>528060810</u> |
| 1.00mm Pitch Easy-On FFC/FPC Connector, Right-Angle, Non-ZIF, Top Contact Style Receptacle, 8 Circuits | <u>528070810</u> |
| 1.00mm Pitch Easy-On FFC/FPC Connector, Surface Mount, Right-Angle, Non-ZIF, Bottom Contact Style, 8 Circuits | <u>528520870</u> |