

COAST

XPH30R MULTI-PURPOSE HEAD TORCH



DUAL POWER

ZITHION-X™ Rechargeable — Also works with CR123 Lithium batteries



1000
LUMENS BRIGHT

30
HOUR RUNTIME

DUST RESISTANT **WEATHER PROOF**
IP54

POWER SOURCES:
Li ION OR LITHIUM
2 x CR123

COAST TRUSTED TOUGH™

FIVE YEAR WARRANTY

XPH30R



A Rechargeable Head torch that Delivers 1000 Lumens in COAST's NEW Durable "Extreme Performance" Line of Portable Lighting Solutions

The COAST XPH30R head torch gives users amazing versatility and powerful brightness. The torch has a maximum lumen output of 1000 on Turbo Mode, and 700 lumens on High.

The XPH30R features a compact, dust-resistant aluminum body that rolls in its bracket for dynamic directional lighting. You can pull the torch out of the bracket to use as a handheld; there is also a magnet on the battery cap which allows you to affix the torch to metal surfaces.

Powered by a COAST ZITHION-X™ rechargeable battery with a real-time battery life indicator, the torch features a twist focus, and four light output options. The torch features COAST's Dual Power™ technology, meaning the torch is also compatible with two CR123 disposable lithium batteries (sold separately).

- 1000 lumens on Turbo Mode with rechargeable battery cell
- COAST ZITHION-X™ rechargeable battery (included), or 2 x CR123 batteries (sold separately)

