

70373

Tank Brush, 205 mm, Hard, Blue



The oval-shaped brush with stiff bristles is effective for scrubbing inside large industrial tanks and other large container-like equipment. The rounded edges work well to clean down the sides of equipment where the entry point is from above. It also fits well into large channel drains.

Technical Data

Item Number	70373
Visible bristle length	40 mm
Material	Polypropylene Polyester Stainless Steel
Suitable for Food Contact (EU 1935/2004), DoC ¹	Yes
Produced according to EU Regulation 2023/2006/EC of Good Manufacturing Practice	Yes
FDA compliant raw material (CFR 21)	Yes
Meets the REACH Regulation (EC) No. 1907/2006	Yes
Use of Phthalates (e.g. Bisphenol A)	No
Is Halal compliant	Yes
Box Quantity	10 Pcs.
Quantity per Pallet (80 x 120 x 200 cm)	480 Pcs
Quantity Per Layer (Pallet)	60 Pcs.
Box Length	545 mm
Box Width	275 mm
Box Height	220 mm
Length	205 mm
Width	130 mm
Height	100 mm
Gross Weight	0,5 kg
Net Weight	0,47 kg
Cubik metre	0,0027 M3
Recommended sterilisation temperature (Autoclave)	121 °C
Max. cleaning temperature (Dishwasher)	93 °C
Max usage temperature (food contact)	80 °C
Max usage temperature (non food contact)	100 °C
Min. usage temperature	-20 °C
Min. pH-value in usage concentration	2 pH
Max. pH-value in Usage Concentration	10,5 pH
Gtin-13 Number	5705020703737
GTIN-14 Number (Box quantity)	15705020703734
Commodity Code	96039099
Country of origin	Denmark

New equipment should be cleaned, disinfected, sterilised and any labels removed, as appropriate to its intended use, e.g. high risk vs. low risk food production areas, general hospital areas vs. intensive care units, before use.