



HelaTape Power - Self-amalgamating Silicone Rubber Tapes

HelaTape Power 800 - Self-amalgamating High Voltage Silicone Rubber Tape

Features and Benefits

- Self-amalgamating, chemically cross-linked silicone rubber tape
- Triangular cross-section with centre line for precise half-overlapping
- Resistant to creepage and surface erosion
- Fuses into solid mass after application
- Weather, UV and Oil resistant
- No adhesive coating
- Recommended use for high temperature silicone insulated cables



HelaTape Power 800 is a silicone rubber tape with triangular cross-section.

MATERIAL	Silicone (SI)
Operating Temperature	+180 °C
Tensile Strength	3.5 MPa
Elongation at break	400 %
Dielectric Strength	23.5 kV/mm



TYPE	Thickness (T)	Width (W)	Length (L)	Colour	Article-No.
HTAPE-POWER800	0.51	25.0	9.1 m	Grey (GY)	711-00400

All dimensions in mm. Subject to technical changes.
Minimum Order Quantity (MOQ) may differ from package content.