

Delivering high level of comfort and chemical protection

- Advanced defenses: AlphaTec® 38-002's new water based butyl formulation offers superior protection against highly aggressive chemicals, including aldehydes, ketones, solvent esters and concentrated mineral acids
- Improved ergonomics: Designed for comfort, AlphaTec® 38-002 industrial gloves feature a unique butyl formulation to facilitate a soft feel, protecting hands while facilitating donning and doffing
- Enhanced flexibility: Ultra soft water based butyl formulation maximizes flexibility and dexterity
- Strengthened grip: Features a raised diamond pattern, enhancing grip and ensuring safer handling

Industries

- Automotive
- Raw material preparation
- Warehousing
- Chemical

Applications

- Equipment repair & maintenance
- Loading and unloading of process equipment
- Handling incoming goods
- Filling, blending and charging of raw materials
- Transferring liquids and solids
- Opening and draining pumps valves or lines
- Transferring liquids and solids between vessels and tanks and process equipment
- Unexpected leakages spills or other releases
- Supervision of running operation
- Blending, compounding solids and/or liquids
- Charging and blending raw materials



Key Features

Delivers high levels of protection against Ketones and Solvents with unparalleled levels of comfort and flexibility

- Improved water based butyl delivering a high level of chemical protection
- Raised diamond grip pattern for enhanced grip in wet and dry
- Unprecedented levels of dexterity and tactility in a butyl glove
- Extended length for forearm protection



Performance Standards



Specifications

BRAND STYLE	DESCRIPTION	SIZE	LENGTH	COLOR	PACKAGE
AlphaTec® 38-002	Liner Material: N/A Coating Material: Butyl Polymer	7, 8, 9, 10, 11	350	Black	1 pair per bag, 36 bags per carton

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 210
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306,
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

Canada

Ansell Canada Inc.
105, rue Lauder
Cowansville (Québec)
J2K 2K8, Canada
T: 1 800 363-8340
F: 1 888 267-3551

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending:
www.ansell.com/patentmarking © 2025 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.