



Rexel Choices Foolscap Polypropylene Lever Arch File

Co-ordinate your workspace with the Rexel Choices range. High quality foolscap lever arch file for professional organisation of documents at home or in the office. Consistently precise closing even after 10,000 uses thanks to the patented No.1 mechanism. 75mm wide spine can hold up to 500 A4 sheets.

Colour	Number	EAN code
black	2115511	5028252580212
blue	2115512	5028252580229
red	2115513	5028252580236
green	2115514	5028252580243
white	2115515	5028252580250

Attributes

- Co-ordinated Rexellence: co-ordinate with other products from the Rexel Choices range
- Patented No.1 mechanism with outstanding locking force for consistently precise closing, guaranteed to close reliably even after 10,000 uses
- Perfect alignment of pins and arches even when file is completely full
- Replaceable spine pocket labels for easy identification of content
- Thumbhole, cover lock and protected metal edges for easy handling and secure document storage
- 500 sheet capacity (80 gsm)
- 3 year guarantee on the mechanism, FSC® certified

Specifications

Number	2115512
Colour	blue
Dimensions (W x H x D)	72 x 348 x 290 mm
For Format	Foolscap
Spine Label	Spine pocket for exchangeable cardboard spine label
Capacity	500 sheet (80gsm)
Spine Width (mm)	75
Slotted Cover	yes
Reinforced Edges	yes
Thumb Hole	yes
Weight	470 g
Pallet quantity	240
EAN code	5028252580229

