



## Main

Range of product	OsiSense XC
Series name	Standard format
Product or component type	Limit switch lever
Device short name	ZCKY
Product compatibility	XCKJ XCKL XCKM XCKS
Associated head	ZCKD05 ZCKE05
Type of operator	Thermoplastic spring return round rod lever (round rod 6 mm, L = 200 mm)
Positive opening	Without
Environmental characteristic	Low temperature Standard environment

## Complementary

Movement of operating head	Rotary
Switch actuation	By any moving part
Type of approach	Lateral approach

## Environment

Ambient air temperature for operation	-40...20 °C for low temperature -25...70 °C for standard environment
Ambient air temperature for storage	-25...70 °C for standard environment -25...70 °C for low temperature
RoHS EUR conformity date	4Q2009
RoHS EUR status	Will be compliant