



Sample photo

Order symbol: CAB P 403017
Product nbr: 8104304
Description: Polyester cabinet
Remarks: Grey door

EAN: 6418074050014
El. number:
 Finland 3424135
 Denmark 8212018015
 Sweden 2539819

Including: Cabinet base, door with PUR gasket, 3mm double bit lock(s) with transport and plastic key, screws for mounting plate/DIN-rail and wall fastening lugs with screws. Wall mounting screws not supplied.

Dimensions:		L	W	H	Rating:
mm:		400	300	170	Ingress Protection (EN 60529): IP 66
inch:		15.7	11.8	6.7	Impact Resistance (EN 50102): IK 10
Materials:					
Material:		GRP			
Base colour:		RAL 7032			
Cover colour:		RAL 7032			
Cover screws material:		Stainless steel			
Gasket material:		Polyurethane			
Temperatures:					
Short term:		-50 ... 150 °C			
Continuous:		-40 ... 70 °C			
Short term:		-60 ... 302 °F			
Continuous:		-40 ... 158 °F			
Accessories:					
MP 4030		Mounting plate			
					Electrical insulation: Totally insulated
					UV resistance: UL 508
					Flammability Rating (UL 746 C 5): UL 94 5V
					Glow Wire Test (IEC 695-2-1) °C: 960
					UL Type: UL TYPE 3, 3R, 3S, 4, 4X, 12, 13
Certificates:					

