

FEATURES

- Halogen free sheath
- High performance cable assembly
- Impedance of 50 ohms
- Cable assembly is available with various cable lengths
- Cable diameter of 1.37

RS PRO Black Female SMA to Female U.FL RF Coaxial Cable, 50 Ω

RS Stock No.: 794-2825



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

From the trusted brand RS PRO, comes a range of high quality Male SMA to Male RG402 Coaxial Cable. Constructed out of industry-standard components, these flexible cables have been designed to carry signals over long distances and are easy to install. These U.FL RF coaxial 50-ohm cable These coaxial cables have SMA bulkhead crimp jack on one end that comes with a cable nut, washer and an SMA plug on the other end.

General Specifications

Coaxial Type	RF
Connector A	Female SMA
Connector B	Female U.FL
Terminated/Unterminated	Terminated
Sheath Colour	Black
Applications	Connecting radio transmitters and receivers with their antennas, Computer network (Internet) connections, Feeding satellite signals through to your TV.

Electrical Specifications

Voltage Rating	250V
Characteristic Impedance	50 Ω
Maximum Operating Frequency (GHz)	DC 3GHz
Voltage Withstand (VRMS)	750Vrms min

Mechanical Specifications

Length	100mm
Outer Diameter	1.37mm
Cable Shape	Coaxial

Approvals

Compliance/Certifications

EN61340

