# Reciprocating Saw LXT®

# DJR185

18V • 0 – 3 300 min$^{-1}$ • 13 mm

**Compact reciprocating saw for light use, also accepts jigsaw bits**

A straight-framed light and small reciprocating saw offers access to tight places. Two separate switches enable diverse working postures. Stroke length of 13 mm, stroke rate can be adjusted between 0 – 3 300 min$^{-1}$ from a switch. LED light.



LXT

## Technical specifications

| | |
|---|---|
| Nominal Battery Voltage | 18 V |
| Voltage LXT | ✓ |
| Strokes per Minute (SPM) | 0 - 3000 min$^{-1}$ |
| Length of Stroke | 13 mm |
| Max. Cutting Capacity in Wood (90°) | 50 mm |
| Max. Cutting Capacity in Steel Pipe | 50 mm |
| Sound Pressure Level ($L_{pA}$) | 79 dB(A) |
| Noise Uncertainty (K Factor) | 3 dB(A) |
| Tool weight with battery | 1,5 - 1,8 kg |
| Product Dimensions (L x W x H): | 398 x 81 x 220 mm |
| Battery Chemistry (Ni-Cd / Ni-MH / Li-ion) | Li-ion |
| Vibration Level, Cutting Boards | 8,0 m/s$^2$ |
| Vibration Uncertainty (K Factor), Cutting Boards | 1,5 m/s$^2$ |
| Vibration Level, Cutting Wooden Beam | 7,0 m/s$^2$ |
| Vibration Uncertainty (K Factor), | 1,5 m/s$^2$ |

## User benefits

- Two different operating switches for versatile working
- Accepts both Recipro and Jig saw blades
- LED light illuminates the work site
- Ideal for working in tight spaces and overhead applications
- Battery protection system automatically shuts off power when the battery level is low

**Link to product - www.makitauk.com**

# Related products

## Other

User manual

Parts drawing