




Connectors > Automotive Connectors > Connector Housings > ECONOSEAL, CONNECTOR HOUSING



Connector & Housing Type: **Housing for Female Terminals**

Connector System: **Wire-to-Wire**

Number of Positions: **2**

Centerline (Pitch): **4.8 mm [.188 in]**

Sealable: **No**

[All ECONOSEAL, CONNECTOR HOUSING \(90\)](#)

Features

Product Type Features

Connector & Housing Shape	Rectangular
Connector & Housing Type	Housing for Female Terminals
Connector System	Wire-to-Wire
Sealable	No
Hybrid Connector	No
Primary Locking Feature	Integrated in Housing

Configuration Features

Number of Positions	2
Number of Rows	1

Body Features

Cable Exit Angle	180°
Body Material	PA
Primary Product Color	Black

Mechanical Attachment

Mounting Feature	Without
Terminal Position Assurance	No
Strain Relief	Without



Mating Alignment Type	Polarization Slot
Mating Alignment	With
Connector Mounting Type	Cable Mount (Free-Hanging)

Housing Features

Centerline (Pitch)	4.8 mm[.188 in]
--------------------	-----------------

Dimensions

Product Width	27.6 mm[1.08 in]
Product Length	20.6 mm[.811 in]
Product Height	19.8 mm[.779 in]

Operation/Application

Circuit Application	Signal
---------------------	--------

Packaging Features

Packaging Quantity	1600
Packaging Method	Box

Other

Serviceable	No
Connector Position Assurance Capable	No

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer



This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 344274-1
2 WAY TAB HOUSING BLACK ECONO

Also in the Series | Econoseal

Automotive Connector Caps & Covers
(1)

Automotive Connector Locks & Position Assurance(25)

Automotive Housings(62)

Automotive Seals & Cavity Plugs(17)

Automotive Terminals(47)

Insertion & Extraction Tools(7)

Other Automotive Connector Accessories(5)

PCB Headers & Receptacles(4)



Primary Wire(1)

Customers Also Bought



TE Part #5069836053
CGPT-4.8/2.4-0-20MM



TE Part #344068-1
.250\"SPEC.F.REC.(PLATED)



TE Part #5-1563898-9
53POS, MIXED,REC HSG,ASSY



TE Part #968138-2
MPQ2,8 Sn tab LL EDS >0,5-1,0



TE Part #2295154-4
22POS,0.64 GENER. Y,REC HSG,ASSY, SLD



TE Part #7-2151579-7
OCEAN_2.0_SPARE_PART_KIT-120F155O



TE Part #CD05883001
ACW0219-0.75-12L(NS)



TE Part #CU7436-000
RNF-150-1/2-0-45MM



TE Part #1564429-2
26POS,MQS,REC HSG,ASSY



TE Part #5-1355956-5
47 WAY ABS CONNECTOR

Documents

Product Drawings

2WAY RECEPTACLE HSG.BLACKECONO

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_344275-1_H_c-344275-1-h.2d_dxf.zip



English

Customer View Model

[ENG_CVM_CVM_344275-1_H_c-344275-1-h.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_344275-1_H_c-344275-1-h.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[Econoseal Connector Series](#)

English