



ENGLISH

Datasheet

Stock No: 137-1151

# RS Pro Natural Nylon Cable Tie, 295mm x 3.6 mm, SL



Image representative of range

## Product Details

Cable ties, type SES-QUICK

Transparent polyamide 6.6.

Cable Ties - Nylon



## Specifications

Length	295mm
Width	3.6 mm
Colour	Natural
Material	Nylon 66
Quantity	1000
Minimum Operating Temperature	-40°C
Maximum Operating Temperature	+85°C
Series	SL
Tensile Strength	130N
Maximum Bundle Diameter	76mm