

## FEATURES

- **UV Resistant:** Ensures durability and longevity in outdoor applications
- **Tensile Strength of 22 kg:** Provides strong and secure fastening for heavy-duty applications
- **Operating Temperature Range -40 °C to 85 °C:** Suitable for use in extreme temperature conditions
- **Made from Polyamide:** Offers excellent resistance to wear and tear
- **Black Colour:** Provides a discreet and professional appearance
- **Maximum Bundle Diameter of 80 mm:** Accommodates a wide range of cable sizes
- **Width of 4.5 mm:** Balances strength with flexibility for various applications

## RS PRO Standard Cable Tie, 300 mm Black

RS Stock No: 642-832



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

### Product Description

The RS PRO Standard Cable Tie is a versatile and reliable solution for bundling and securing cables. Made from durable polyamide, this cable tie is designed to withstand various environmental conditions, making it ideal for both indoor and outdoor use. Its UV resistance ensures longevity even when exposed to sunlight, while its robust tensile strength provides secure fastening.

### General Specifications

Colour	Black
Product Type	Cable Tie
Sub Type	Standard
Tensile Strength	22 kg

### Protection Category

Fire Behaviour	UL 94 V-2
UV Resistant	Yes

### Mechanical Specifications

Length	300 mm
Material	Polyamide
Maximum Bundle Diameter	80 mm
Width	4.5 mm

### Operation Environment Specifications

Maximum Operating Temperature	85 °C
Minimum Operating Temperature	-40 °C

### Approvals

Standards/Approvals	ISO 9001 SGS, REACH, RoHS, UL94V-2
---------------------	------------------------------------