

ASCM 12 QC

4-speed cordless drill/driver

Order number:: 7 116 10 61 00 0



The most powerful 12V cordless drill/driver with brushless motor, 4-speed gearbox and removable drill chuck.

- Brushless FEIN PowerDrive motor, powerful and maintenance-free for maximum efficiency and service life.
- Solid metal removable drill chuck for excellent load handling under the toughest conditions.
- The optimum cutting speed for any drill diameter thanks to 4-speed solid metal gearbox.
- Speed 4 for drilling 6 mm in metal at 2500 rpm.
- Speed 1 for powerful thread cutting.
- Optimum speeds for self-drilling screws.
- Speeds can be easily metered for work with stepped drill bit.
- Drill chuck with spindle lock and chucking force safety device.
- Compact 150 mm length (without drill chuck).
- 2.5 Ah battery capacity for up to 400 screw connections (5x 40 mm).
- FEIN SafetyCell technology. Protects the battery and tool from overload, overheating and total discharge.
- The battery charge can be read off the battery.
- Includes belt holder and magnetic bit holder.
- Bright LED light on housing.
- One charger for all FEIN Li-ion batteries of all voltage classes.



ASCM 12 QC

4-speed cordless drill/driver

Order number:: 7 116 10 61 00 0

Technical data

Battery voltage	12 V
Battery capacity	2,5 Ah
Motor	brushless
Gearbox	4-speed
Interface	QuickIN
Speed, no load	400 / 700 / 1 400 / 2 500 rpm
Max. torque (hard/soft)	40 / 20 Nm
Torque levels	20 + 1
Drill chuck clamping width	1,5 - 13 mm
Fastening	8 x 200 mm
Capacity in steel Ø	13 mm
Capacity in wood Ø	40 mm
Weight with battery	1,1 kg
Cordless	X

Included in price::

1 cordless drill/driver
2 battery packs (Li-ion)
1 rapid charger ALG 50
1 belt clip
1 bit holder
1 plastic carrying case