



## TAHBE8610S-TAHBE8620S ERGO™ Insulated Phillips Screwdrivers with Kevlar String









### PRODUCT DETAILS

- For Phillips head screws
- For work on live equipment up to 1000 V
- Phosphate finished tip
- Three-component handle developed according to the scientific ERGO™ process
- Soft material with ridged surface provides superior grip and greater force transmission
- Flat face to prevent rolling
- Colour-coded handle with the screw type symbol on the domed end
- High-performance alloy steel blade
- Standards: ISO 8764, IEC 60900, VDE certified
- Suitable for working at height
- Coloured tags with maximum weight for proper match with lanyard
- Compliant with DROPS best practices



### PRODUCT ATTRIBUTES

Product						
<b>TAHBE-8610S</b>	PH1	80 mm	122 mm	27 mm	202 mm	70 g
<b>TAHBE-8620S</b>	PH2	100 mm	122 mm	36 mm	222 mm	108 g
<b>TAHBE-8630S</b>	PH3	150 mm	122 mm	36 mm	272 mm	170 g
<b>TAHBE-8640S</b>	PH4	190 mm	165 mm	36 mm	350 mm	240 g

Follow the Fish!

