

RCD Protected Cable IP 54 with Powerblock 5 m black H07RN-F 3G1.5

For universal outdoor use and permanent use on sites, IP 54.



**ENGINEERED IN
GERMANY**



Product number 1168720010
EAN 4007123647736

DESCRIPTION

- Ideal for hard outdoor use.
- With circuit breaker plug 30 mA to protect against electrical shocks.
- Function test indicator.
- When touched by current-conducting leads or parts, the current supply is automatically interrupted to protect against dangerous bodily injury and electric shocks.
- Quality rubber cable with 4-way dust- and water-jet protected safety socket outlets.
- Residual current: 30 mA.
- Working temperature: -25 °C bis 40 °C.

TECHNICAL DATA

Cable quality	Rubber-Neoprene	Permanent sockets	4
Cable length	5 m	Socket outlets total	4
Cable designation	H07RN-F 3G1,5	Max. current carrying capacity	16 A
Cable colour	black	Colour	yellow

PACKAGING, DIMENSIONS AND WEIGHTS

UP	1	Weight of product (including packaging)	1.29 kg
Weight of product (without packaging)	1.28 kg	Dimension LxWxH (incl. packing)	32 cm x 30.5 cm x 9 cm
Dimension LxWxH (without packing)	32 cm x 30.5 cm x 9 cm		

SCOPE OF DELIVERY

RCD Protected Cable IP54 with Powerblock